

BYC-1500

Simplified Coating Machine



**EQUIPMENT
TECHNICAL PARAMETER**

南京翰洋智能设备有限公司
NANJING HANYOO PHARMATECH CO., LTD.



BYC-1500 Coating Machine



MACHINE APPLICATION

This machine is mainly used for making pellet, coating film on tablets. It can also be used for making ball shape products or granules, mixing, and polishing, etc.

Such as: chocolate polishing, peanut coating, coating sugar, adding flavor, producing pearl dumplings, and pelletizing the desiccant&aluminium hydroxide, porcelain ball making, etc.

This machine consist of main body, worm wheel box, coating pan, heating device, blower, blower, electrical equipment, etc. The transmission process that the motor drive the worm wheel and worm via triangle belt make the coating pan rotate. Then the material erithe and revolve up and down in the coating pan, so that even mixing, pelletizing and polishing can be completed well.

TECHNICAL PARAMETER

MODEL	BYC-1500
Dia Sugarcoating Dish(mm)	1500
Capacity(kg/time)	200-300
Rotation Speed (r/min)	26
Power Of Motor(KW)	5.5
Power Of Fan(KW)	0.37
Electric Heating Power(kw)	6
Overall Size(mm)	1500*1500*1980
Weight(kg)	600

A dark blue horizontal banner featuring various medical icons in a lighter blue color. The icons include a blister pack of pills, a medicine bottle with a cross, two crossed capsules, a pill bottle, two pills, a syringe, and another blister pack of pills.

HANYOO

翰洋科技

Add:No.380 Sanqiaogeng,Gaochun District,Nanjing,China

Tel:+86-025-5621 6295

[Http://www.hanyoopm.com](http://www.hanyoopm.com)