

# BYC-800

## Simplified Coating Machine



**EQUIPMENT  
TECHNICAL PARAMETER**

**南京翰洋智能设备有限公司**  
NANJING HANYOO PHARMATECH CO., LTD.



## BYC-800 Coating Machine



### MACHINE APPLICATION

This machine is mainly used for making pellet, coating film on tablets. It can also be used for making ball shape products or granules, mixing, and polishing, etc.

Such as: chocolate polishing, peanut coating, coating sugar, adding flavor, producing pearl dumplings, and pelletizing the desiccant&aluminium hydroxide, porcelain ball making, etc.

This machine consist of main body, worm wheel box, coating pan, heating device, blower, blower, electrical equipment, etc. The transmission process that the motor drive the worm wheel and worm via triangle belt make the coating pan rotate. Then the material erithe and revolve up and down in the coating pan, so that even mixing, pelletizing and polishing can be completed well.

## TECHNICAL PARAMETER

MODEL	BYC-800
Dia Sugarcoating Dish(mm)	800
Capacity(kg/time)	30-50
Rotation Speed (r/min)	36
Power Of Motor(KW)	1.5
Power Of Fan(KW)	0.12
Internal heating power (kw)	3
External heating power (kw)	3
Spray gun model	ST-6
Overall Size(mm)	1000×800×1430
Weight(kg)	205

A dark blue horizontal banner featuring various white line-art icons related to medicine and healthcare. The icons include a blister pack of pills, a medicine bottle with a cross, two crossed capsules, a pill bottle, two overlapping pills, a syringe, and another blister pack.

# **HANYOO**

**翰洋科技**

Add:No.380 Sanqiaogeng,Gaochun District,Nanjing,China

Tel:+86-025-5621 6295

[Http://www.hanyoopm.com](http://www.hanyoopm.com)